













Assembly Instructions

Morse Work Table 1400d


A 4 Legs		B 6 & 8 Legs							
									
MSDC316	MSDC324	MSDG328	MSDG336	MSDG340	MSDG344	MSDG348	MSDG356	MSDG364	
Morse Work Table — 1600w x 1400d — 4 leg	Morse Work Table — 2400w x 1400d — 4 leg	Morse Work Table — 2800w x 1400d — 6 leg	Morse Work Table — 3600w x 1400d — 6 leg	Morse Work Table — 4000w x 1400d — 8 leg	Morse Work Table — 4400w x 1400d — 6 leg	Morse Work Table — 4800w x 1400d — 8 leg	Morse Work Table — 5600w x 1400d — 8 leg	Morse Work Table — 6400w x 1400d — 8 leg	
									
MSDC516	MSDC524	MSDG528	MSDG536	MSDG540	MSDG544	MSDG548	MSDG556	MSDG564	
Morse Bar Height Work Table — 1600w x 1400d — 4 leg	Morse Bar Height Work Table — 2400w x 1400d — 4 leg	Morse Bar Height Work Table — 2800w x 1400d — 6 leg	Morse Bar Height Work Table — 3600w x 1400d — 6 leg	Morse Bar Height Work Table — 4000w x 1400d — 8 leg	Morse Bar Height Work Table — 4400w x 1400d — 6 leg	Morse Bar Height Work Table — 4800w x 1400d — 8 leg	Morse Bar Height Work Table — 5600w x 1400d — 8 leg	Morse Bar Height Work Table — 6400w x 1400d — 8 leg	

ASSEMBLY STEPS


- 1 Build Table Frame
- 2 Add Table Top
- 3 Basket Options
- 4 Add Power and Data to Basket
- 5 Add Basket to Table Top
- 6 Cable layouts
- 7 Add Accessories

	
2 X PEOPLE	TX30 BIT
	
13MM SPANNER OR SOCKET	#8 POZIDRIV SCREWDRIVER


Build Table **A** Frame
Morse Work Table 1400d
4 Leg



STEP
1





TX30 BIT




13MM SPANNER
OR SOCKET

	X4
M6X20TXCSPATCH	
	X8
M8FLANGENUTSS	
	X8
M8X75CARRIAGEBL	

Build Table **B** Frame
Morse Work Table 1400d
6 & 8 Leg





TX30 BIT



13MM SPANNER
OR SOCKET

	X2 PER LEG SET
M6X20TXCSPATCH	
	X4 PER LEG SET
M8FLANGENUTSS	
	X4 LEG SET
M6X25TXCSPATCHBL	

1






X1 PER LEG

M6X20TXCSPATCH

A

2





LEG SET

BEAM

A

3




X8

M8FLANGENUTSS





X8





M8X75CARRIAGEBL




B 2




B 3





Add **A** Table Top
Morse Work Table 1400d
4 Legs





STEP
2




Add **B** Table Top
Morse Work Table 1400d
6 & 8 Legs





	
X4 PER LEG SET	X2 PER BRACE CLIP
BRACE CLIP	M6X16TXFLANGE
	
X4 PER LEG SET	X4 PER BEAM
M6X16TXFLANGE	M6X16TXFLANGE





		
LEG SET	BEAM	BRACE CLIP


Basket Options Morse Work Table 1400d

A 4 Legs

	
MSDC316 or MSDC516	MSDC324 or MSDC524
1600w x 1400d	2400w x 1400d
— Basket Long	Basket Short x2 Basket Long

B 6 & 8 Legs

						
MSDG328 or MSDG528	MSDG336 or MSDG536	MSDG340 or MSDG540	MSDG344 or MSDG544	MSDG348 or MSDG548	MSDG356 or MSDG556	MSDG364 or MSDG564
2800w x 1400d	3600w x 1400d	4000w x 1400d	4400w x 1400d	4800w x 1400d	5600w x 1400d	6400w x 1400d
— Basket Long x2	Basket Short x2 Basket Long x2	— Basket Long x3	Basket Short x4 Basket Long x2	Basket Short x2 Basket Long x3	Basket Short x4 Basket Long x3	Basket Short x6 Basket Long x3




STEP

3





Add Power & Data to Basket

Morse Work Table 1400d




STEP
4


BY HAND




Add Basket to Table Top Morse Work Table 1400d


7





8



9



10



STEP
5



#8 POZIDRIV
SCREWDRIVER













X4 PER BASKET

PCLIP48ALU




X4 PER BASKET

4X16PANWOODSCREW



Cable layouts Morse Meeting Table




STEP
6


Cable Managed Leg can be placed in any location

Alternative cable management route into perimeter mounted power source

Add Accessories Morse Table



*These accessories can only be used on a Morse Table with a central channel.



STEP
7